

## IH Equipment

The listed equipment gives the industrial hygienist the basic functions to run an Industrial Hygiene program. This is not a complete listing of our industrial hygiene laboratory's equipment and total capability. If you are an Army employee and wish to receive information on any of our equipment please email:

[USAPHC-IHEquipmentRequest@amedd.army.mil](mailto:USAPHC-IHEquipmentRequest@amedd.army.mil)



SKC CONSTANT FLOW AIR SAMPLING PUMP MODEL 224-44XR

**Description:** The constant flow air sampler SKC model 224-44XR has a broad range of applications. It has been used by the Industrial Hygiene Equipment Lab for 10 or more years.

### Specifications:

Flow Range: 5–5000 mL/min

Weight: 3.3 ounces

Flow Control:  $\pm 5\%$  set point, constant flow

Run Time: 8 hours

Battery Assembly: rechargeable nickel cadmium; Intrinsically Safe for UL<sup>®</sup> listed for explosive gas and dust atmospheres of Class 1, Division 1 and 2, Groups A, B, C, D, Class II, Division 1 and 2, Groups E, F, and G, Class III, Temperature Code T3C, MSHA and ATEX approved models contact SKC